


Magnet presentation card

gif-142 / A4 / Parts overview - NOT A CUTTING SHEET

USE THE FOLLOWING PATTERN SHEETS AT ACTUAL SIZE.

These miniature views identify the supplied patterns; they are deliberately reduced.



1. Pattern 1

1 pattern sheet supplied. Printed details are not cut lines unless explicitly marked.

Solid cut boundary / dashed score / shaded joining area. Read the full instructions.

Dry-fit the parts before gluing. Keep this overview beside the full-size pattern sheets.



Print at actual size / 100%. Disable fit-to-page.
Use the paper edition that matches the printer tray.

Magnet presentation card

gif-142 / A4 / Pattern 1

Magnet



Print at actual size / 100%. Disable fit-to-page.
Use the paper edition that matches the printer tray.

Magnet presentation card

gif-142 / A4 / Instructions

PURPOSE

Magnet presentation card developed as a fixed-size paper pattern with separate cut, fold and joining marks. Use the stated drawing sizes and make an empty trial before choosing material or contents.

DRAWING FACTS

- Presentation card: 85 x 110 mm. Marked attachment locations are design positions, not retention/load ratings.

MATERIALS

Plain paper for a first trial, a ruler, scissors and a blunt scoring tool; adult help for internal cuts.

HOW TO USE THESE PAGES

1. Cut the 85 x 110 mm card and write the item name on its heading line.
2. Use the outlined center area to position an expendable display sample. Attach it with a removable method suited to that sample; the outline is a placement guide, not a cutout.
3. Check that the sample removes cleanly and the card stays flat. No fold, sleeve or locking part is supplied.

LIMITS AND CHECKS

- Nominal drawing dimensions are not a tested usable-capacity, load, mailing, food-contact or archival specification.
- Do not place valuable, wet, hot or breakable items in an unreviewed paper prototype.
- Trial: Measure the 50 mm reference and at least two named panel dimensions.
- Trial: Assemble an empty plain-paper trial; record closure, seam, clearance and material behavior.



50 mm print check

Print at actual size / 100%. Disable fit-to-page.
Use the paper edition that matches the printer tray.